




**VF Series, UMC Series, EC-400, GM-2**

8100/10,000-rpm, Inline-Drive Spindle

40 Taper – 30 hp

Standard: VF-1 to VF-12, EC-400, GM-2, UMC-500/750/1000 (8100 rpm)

Optional: VF-1 to VF-12, EC-400, GM-2, UMC-500/750/1000 (10,000 rpm)



Values shown are 200% spindle load

1/29/2016




**VF Series, UMC Series, EC-400, GM-2**

8100/10,000-rpm, Inline-Drive Spindle

40 Taper – 22.4 kW

Standard: VF-1 to VF-12, EC-400, GM-2, UMC-500/750/1000 (8100 rpm)

Optional: VF-1 to VF-12, EC-400, GM-2, UMC-500/750/1000 (10,000 rpm)




Values shown are 200% spindle load

1/29/2016




**VF/VM Series, UMC Series, EC-400, GM-2**  
15,000-rpm, Inline-Drive Spindle  
40 Taper – 30 hp  
Standard: None  
Optional: VM, VF-1 to VF-12, UMC Series, EC-400, GM-2



Values shown are 200% Spindle Load  
1/29/2016



**VF/VM Series, UMC Series, EC-400, GM-2**  
15,000-rpm, Inline-Drive Spindle  
40 Taper – 22.4 kW  
Standard: None  
Optional: VM, VF-1 to VF-12, UMC Series, EC-400, GM-2



Values shown are 200% Spindle Load  
1/29/2016