




Toolroom Mill / Mini Mill Series

4000/6000-rpm, Belt-Drive Spindle

40 Taper – 7.5 hp

Standard: TM-1/2/3 (4000 rpm), TM-1P/2P/3P, MM-1/2 (6000 rpm)

Optional: 6000 rpm – TM-1/2/3



Values shown are 200% spindle Load

1/29/2016




Toolroom Mill / Mini Mill Series

4000/6000-rpm, Belt-Drive Spindle

40 Taper – 5.6 kW

Standard: TM-1/2/3 (4000 rpm), TM-1P/2P/3P, MM-1/2 (6000 rpm)

Optional: 6000 rpm – TM-1/2/3




Values shown are 200% spindle Load

1/29/2016



Toolroom Mill Series, Mini Mill, Mini Mill 2
10,000-rpm, Grease-Packed Spindle
40 Taper – 7.5 hp
Standard: None
Optional: TM Series, MM, MM2 (excluding EDU models)




Values shown are 200% spindle load

1/2/19



Toolroom Mill Series, Mini Mill, Mini Mill 2
10,000-rpm, Grease-Packed Spindle
40 Taper – 5.6 kW
Standard: None
Optional: TM Series, MM, MM2 (excluding EDU models)



Values shown are 200% spindle load

1/2/19