




TL-1, TL-2
1800/3000-rpm, Belt-Drive Spindle
A2-5/A2-6 – 10 hp
Standard: TL-1/TL-2 (1800 rpm)
Optional: TL-1/TL-2 (3000 rpm)




Values shown are 200% spindle load

1/29/2016



TL-1, TL-2
1800/3000-rpm, Belt-Drive Spindle
A2-5/A2-6 – 8.9 kW
Standard: TL-1/TL-2 (1800 rpm)
Optional: TL-1/TL-2 (3000 rpm)



Values shown are 200% spindle load

1/29/2016