




**Drill/Tap, Drill/Mill Series**  
10,000-rpm, In-line-Drive Spindle  
30/40 Taper – 15 hp  
Standard: DT/DM Series  
Optional: None




Values shown are 200% spindle load

1/2/19



**Drill/Tap, Drill/Mill Series**  
10,000-rpm, In-line-Drive Spindle  
30/40 Taper – 11.2 kW  
Standard: DT/DM Series  
Optional: None




Values shown are 200% spindle load

1/2/19



**Drill/Tap, Drill/Mill Series**  
12,000/15,000-rpm, Inline-Drive Spindle  
30/40 Taper – 15 hp  
Standard: None  
Optional: DT/DM Series




Values shown are 200% spindle load

1/2/19



**Drill/Tap, Drill/Mill Series**  
12,000/15,000-rpm, Inline-Drive Spindle  
30/40 Taper – 11.2 kW  
Standard: None  
Optional: DT/DM Series



Values shown are 200% spindle load

1/2/19