




ST Series
3400-rpm, Belt-Drive Spindle
A2-6 – 30 hp
Standard: ST-25, ST-25Y, ST-30, ST-30Y
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
3400-rpm, Belt-Drive Spindle
A2-6 – 22.4 kW
Standard: ST-25, ST-25Y, ST-30, ST-30Y
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
3400-rpm, Gearbox Drive
A2-6 – 30 hp
Standard:None
Optional: ST-30, ST-30Y




Values shown are 200% spindle load

1/29/2016



ST Series
3400-rpm, Gearbox Drive
A2-6 – 22.4 kW
Standard:None
Optional: ST-30, ST-30Y




Values shown are 200% spindle load

1/29/2016



ST Series
4500-rpm, Belt-Drive Spindle
A2-6 – 30 hp
Standard: DS-30Y
Optional: ST-30/Y




Values shown are 200% spindle load

1/29/2016



ST Series
4500-rpm, Belt-Drive Spindle
A2-6 – 22.4 kW
Standard: DS-30Y
Optional: ST-30/Y



Values shown are 200% spindle load

1/29/2016