



Intertek
9700845

ETL LISTED
CONFORMS TO
NFPA STD 79
ANSI/UL STD 508
UL SUBJECT 2011
CERTIFIED TO
CAN/CSA STD C22.2 NO. 73



MODEL

EC-400FP

HAAS AUTOMATION, INC, OXNARD, CA. 93030

SERIAL NUMBER 2054740

DATE OF MFG 12/2015

VOLTAGE 440

PHASE 3

HERTZ 50/60

FULL LOAD 35 AMPS

LARGEST LOAD 33 AMPS

SHORT CIRCUIT INTERRUPTING CAPACITY - 10,000 AMPS

WIRING DIAGRAM 96 0284

SHORT CIRCUIT CURRENT 5,000 Amps RMS SYMMETRICAL

ARC FLASH RATING: 208-240VAC MODELS HRC-1,
360-480VAC MODELS HRC-2.

NEMA TYPE 1 ENCLOSURE-FOR INDOOR USE ONLY.
OVER CURRENT PROTECTION PROVIDED
AT MACHINE SUPPLY TERMINALS.

MADE IN U.S.A.

P/N 29-10048

















GAUGES 1	GAUGES 2	CONFIGURATION	/0	/0 2	INPUTS 2	PALLET	TOOL CHANGER	LUBE
CONFIGURATIONS					MACHINE DATA			
MODEL EC-400PP SN: 2054740					Time 06-08-2021, 15:30:12			
SOFTWARE VER M18.29B					RUN TIME 18957:07			
Link: Jun 17 2016, 14:08:58					BILL TIME 4903:48:38			
By: mteitel					TOOL CHANGES 110775			
P4: TP13320					APC COUNT 9673			
CL: 85703					POWER ONS 115			
ROTARY VER 22					NETWORK INFORMATION			
FLOPPY FV 6 14.011					Host Name HAASMachine			
VIDEO VV 41					Domain			
MOCON#1 17.28					DNS Server 10.1.1.11			
Monitor 2.02					MAC Address 00:1E:BF:01:4A:DF			
FPGA 1.15B					DHCP Enabled YES			
MOCON#2 17.28					DHCP Server 10.1.1.92			
Monitor 2.02					IP Address 0.0.0.0			
FPGA N/A					Subnet Mask 0.0.0.0			
SKBIF VER 49 (SKBIF-2 MODE)					Gateway			
RJH-C								
< 3 of 9 >								
CLIPBOARD								

