

ETL LISTED
CONFORMS TO
NFPA STD 79
ANSI/UL STD 508
UL SUBJECT 2011
CERTIFIED TO
CAN/CSA STD C22.2 NO. 73

9700845

HAAS LATHE MODEL

ST-30SS

HAAS AUTOMATION, INC. OXNARD, CA. 93030

SERIAL NUMBER..... 3085039

DATE OF MFG..... 10/09

VOLTAGE..... 360-480

PHASE..... 3

HERTZ..... 50/60

FULL LOAD..... 40 AMPS

LARGEST LOAD..... 70 AMPS

SHORT CIRCUIT INTERRUPTING CAPACITY - 10,000 AMPS

WIRING DIAGRAM..... 96 0284

SHORT CIRCUIT CURRENT - 5,000 AMPS RMS SYMMETRICAL

ARC FLASH RATING: 208 - 240VAC MODELS HRC-1,
360-480VAC MODELS HRC-2

NEMA TYPE 2 ENCLOSURE - FOR INDOOR USE ONLY







COLLET CLEANED ON

TOOL CALL PLEASE.

GAUGES 1	GAUGES 2	CONFIGURATION	I/O	I/O 2	INPUTS 2	BAR FEEDER	LUBE
CONFIGURATIONS				MACHINE DATA			
MODEL ST30SS SN: 3085039				Time 10-09-2020, 15:20:52			
SOFTWARE VER L11.25B Link: Jun 17 2016, 14:17:36				RUN TIME 11075:08 TOOL CHANGES 1162725 POWER ONS 204			
FLOPPY FV 6 14.011 VIDEO VV 41				NETWORK INFORMATION			
MOCON#1 17.28 Monitor 2.02 FPGA 1.15B				Host Name HAASMachine Domain DNS Server 10.1.1.11 MAC Address 00:1E:BF:01:47:EC DHCP Enabled YES DHCP Server 10.1.1.92 IP Address 0.0.0.0 Subnet Mask 0.0.0.0 Gateway			
MOCON#2 17.28 Monitor 2.02 FPGA N/A							
SKBIF VER 41 (SKBIF-2 MODE) RJH-C							
< 3 of 8 >							
POSITION: (IN)		JOG RATE:		0.0010			
	OPERATOR	WORK G54	MACHINE	DIST TO GO			
X	-0.0001	-0.0001	-0.0001	-0.0001			
Z	0.0000	0.0000	0.0000	0.0000			
B	0.0	0.0	0.0	0.0			