

Technical Details



10 to 18 millimeters 09-0399 & 09-0408			
Measuring Range		Anvil	Washer
10	10.5	10	
10.5	11	10	0.5
11	11.5	11	
11.5	12	11	0.5
12	12.5	12	
12.5	13	12	0.5
13	13.5	13	
13.5	14	13	0.5
14	14.5	14	
14.5	15	14	0.5
15	15.5	15	
15.5	16	15	0.5
16	16.5	16	
16.5	17	16	0.5
17	17.5	17	
17.5	18	17	0.5
18	18.5	18	
18.5	19	18	0.5