

Technical Details



0.4 to 0.7 Inches 09-0109 & 09-0423			
Measuring Range		Anvil	Washer
0.40	0.42	0.40	
0.42	0.44	0.40	0.02
0.44	0.46	0.44	
0.46	0.48	0.44	0.02
0.48	0.50	0.48	
0.50	0.52	0.48	0.02
0.52	0.54	0.52	
0.54	0.56	0.52	0.02
0.56	0.58	0.56	
0.58	0.60	0.56	0.02
0.60	0.62	0.60	
0.62	0.64	0.60	0.02
0.64	0.66	0.64	
0.66	0.68	0.64	0.02
0.68	0.70	0.68	
0.70	0.72	0.68	0.02
0.70	0.72	0.70	
0.72	0.74	0.70	0.02