



Horizontal Mill:  
**EC-400**

The Perfect Solution for  
Production Machining




# EC Series

The Haas EC-400 is a 40-taper horizontal workhorse with a generous 22" x 25" x 22" work envelope, a built-in pallet changer with 400 mm pallets, and a full 4th-axis rotary indexer – making it perfect for your production machining needs.



**40** / **4/5** / **8.1k-15k** / **30-100**  
TAPER      AXIS      RPM      TOOL CAPACITY

## A Rugged 40-Taper HMC with Large Capacity



### SPINDLES

Reliable, high-performance spindles – designed and manufactured by Haas.

#### STANDARD

- 8100-rpm, Inline Direct Drive

#### OPTIONAL

- 10,000-rpm, Inline Direct Drive
- 12,000-rpm, Inline Direct Drive
- 15,000-rpm, Inline Direct Drive



### TOOL CHANGERS

Capacity and speed to minimize your cycle times and boost your productivity.

#### STANDARD

- 30+1 Side-Mount

#### OPTIONAL

- 50+1 Side-Mount
- 100+1 Side-Mount



### CHIPS & COOLANT

Features and options to help your machine do what it does best – make chips efficiently.

- Belt-Type Chip Conveyor
- Through-Spindle Coolant\*
- Automatic Coolant Refill System\*
- Auxiliary Coolant Filter System\*



### HAAS CONTROL

Faster, smarter, and better than ever, with the goal of keeping your spindle turning.

- HaasConnect Remote Monitoring
- Ethernet Connectivity
- User-Definable Macros\*
- DWO/TCPC\*
- Expandable Memory\*
- WiFi Connectivity\*

## Available Models

### EC-400

22" x 25" x 22" travels

**BUILD & PRICE** yours  
at [www.HaasCNC.com](http://www.HaasCNC.com)

**HAAS**