



MACHINE	A	B	D
Description	Additional Clearance from Standard	Ground Clearance	Total Length of CDF Conveyor
UMC-500/500SS	15.4in [391mm]	38.9in [987mm]	120.3in [3131mm]
UMC-750/750SS	17.2in [436mm]	37.4in [950mm]	140.7in [3574mm]
UMC-1000/1000SS/1000SS-P	17.2in [436mm]	37.4in [950mm]	140.6in [3572mm]
UMC-1250/1250SS	17.2in [436mm]	39.8in [1011mm]	148.4in [3769mm]
UMC-1500-DUO/1500SS-DUO	17.2in [436mm]	37.42in [951mm]	165.4in [4200mm]
VC-400/400SS	17.2in [436mm]	40.5in [1027mm]	161.1in [4092mm]
EC-400	17.2in [436mm]	40.5in [1027mm]	161.1in [4092mm]
EC-500/500\50	17.2in [436mm]	40.5in [1027mm]	170.8in [4337mm]
EC-630	TBD	TBD	TBD



MACHINE	A	B	C	D
Description	Additional Clearance from Standard	Enclosure Max to Conveyor connection	Clearance from Machine Enclosure	Clearance for CDF Conveyor Removal
UMC-500/500SS	31.3in [794mm]	9.2in [233mm]	49.4in [1253mm]	108.8in [2762mm]
UMC-750/750SS	25.64in [651mm]	9.2in [233mm]	55.1in [1400mm]	131.7in [3344mm]
UMC-1000/1000SS/1000SS-P	25.3in [642mm]	12.3in [312mm]	54.7in [1389mm]	131.1in [3329mm]
UMC-1250/1250SS	21.56in [547mm]	14.4in [366mm]	45.6in [1159mm]	133.8in [3398mm]
UMC-1500-DUO/1500SS-DUO	25.92in [658mm]	12.9in [328mm]	48.9in [1242mm]	152.8in [3881mm]



MACHINE	A	B	C	D
Description	Additional Clearance from Standard	Enclosure Max to Conveyor connection	Clearance from Machine Enclosure	Clearance for CDF Conveyor Removal
VC-400/400SS	26.0in [660mm]	24.8in [629mm]	22.7in [576mm]	138.9in [3529mm]
EC-400	26.0in [660mm]	22.0in [559mm]	22.7in [576mm]	138.9in [3529mm]
EC-500/500\50	24.0in [611mm]	22.1in [561mm]	22.7in [576mm]	148.8in [3778mm]
EC-630	TBD	20.7in [525mm]	TBD	TBD