






TOP VIEW




FRONT VIEW




THROUGH-BORE




BOTTOM VIEW





LEFT SIDE VIEW




RIGHT SIDE VIEW








STANDARD PLATTER







Ø 12.2in  
[310mm]



0.9in  
[22mm]





REFER TO PAGE 1 FOR BOTTOM BASE DIMENSIONS