




DC 40-Taper Series Drill Centers

Inline-Drive Spindles

40 Taper – 15 hp

Standard: 10,000-rpm

Optional: 12,000-rpm, 15,000-rpm



Values shown are 200% spindle load




DC 40-Taper Series Drill Centers

Inline-Drive Spindles

40 Taper – 11.2 kW

Standard: 10,000-rpm

Optional: 12,000-rpm, 15,000-rpm



Values shown are 200% spindle load