



Product	Part Description	Part Dimensions	Qty	Picture
	Stand Off	Ø 16x30mm	5	
	Stand Off	Ø 16x50mm	5	
	Stand Off	Ø 16x100mm	3	
	Stand Off	Ø 20x30mm	5	
	Stand Off	Ø 20x50mm	5	
	Stand Off	Ø 20x100mm	3	
	Adjustable Stand Off / Screw Jack Assemblies	Ø 16-45-60mm	2	
		Ø 20-45-60mm	2	
	Spring Plunger	N/A	2	
	Level Screw Plunger	N/A	2	
	Magnetic Standoff	Ø 20x25mm	3	
	Pin standoff	Ø 20x25mm	2	
	Spring pusher standoff clamp	Ø 20x25mm	1	
	Adjustable Positioner	45°	2	

Product	Part Description	Part Dimensions	Qty	Picture
	Lengthen Vee- Block	width x height 55x20mm	2	
	Stationary Vee-Block	width x height 20x40mm	2	
	Spring Clip	12x2x50mm	2	
	Spring Clip	12x4x50mm	2	
	Spring Clip Post	Ø6x60mm	2	
	Spring Clip Post	Ø6x100mm	2	
	Adjustable Positioner	10x20x78mm	3	
	Lifting Stem	30x30x25mm	2	



Product	Part Description	Part Dimensions	Qty	Picture
	Clamping Screw	M8x20mm	6	
	Aluminum Step Tip	Ø 16x22mm	2	
	Nylon Step Tip	Ø 16x22mm	2	
	Aluminum Cone Tip	Ø 16x12mm	2	
	Nylon Cone Tip	Ø 16x12mm	2	
	Aluminum Shoulder Tip	Ø 16x12mm	2	
	Nylon Shoulder Tip	Ø 16x12mm	2	
	Aluminum Dome Tip	Ø 16x12mm	2	
	Nylon Dome Tip	Ø 16x12mm	2	
	Aluminum Vee Tip	Ø 16x22mm	2	
	Nylon Vee Tip	Ø 16x22mm	2	



Product	Part Description	Part Dimensions	Qty	Picture
	Aluminum Step Tip	Ø 16x22mm	2	
	Nylon Step Tip	Ø 16x22mm	2	
	Aluminum Cone Top	Ø 16x12mm	2	
	Nylon Cone Tip	Ø 16x12mm	2	
	CMM Aluminum Fixture Plates	M8 400x400x12mm	1	
	Screw	M8x20mm		
	Dirt Catcher		1	
	Anti Rust		1	
	Standoff Wrench	3.8x70mm	1	
	M2.5 Hex wrench	M2.5	1	
	M6 Hex wrench	M6	1	

	Coordinate Button	Coordinate Button case not included. Only Coordinate Buttons are included.	1	
--	--------------------------	---	----------	--