




**ST Series**  
1400-rpm, Gearbox Drive  
A2-11 – 40 hp  
Standard: ST-45, ST-45L  
Optional: None




Values shown are 200% spindle load

1/29/2016



**ST Series**  
1400-rpm, Gearbox Drive  
A2-11 – 29.8 kW  
Standard: ST-45, ST-45L  
Optional: None




Values shown are 200% spindle load

1/29/2016



**ST Series**  
1400-rpm, Extra-Performance Spindle, Gearbox Drive  
A2-11 – 55 hp  
Standard: None  
Optional: ST-45, ST-45L




Values shown are 200% spindle load

1/29/2016



**ST Series**  
1400-rpm, Extra-Performance Spindle, Gearbox Drive  
A2-11 – 41 kW  
Standard: None  
Optional: ST-45, ST-45L



Values shown are 200% spindle load

1/29/2016