




Drill/Tap, Drill/Mill Series
10,000-rpm, In-line-Drive Spindle
30/40 Taper – 15 hp
Standard: DT/DM Series
Optional: None




Values shown are 200% spindle load

1/2/19



Drill/Tap, Drill/Mill Series
10,000-rpm, In-line-Drive Spindle
30/40 Taper – 11.2 kW
Standard: DT/DM Series
Optional: None




Values shown are 200% spindle load

1/2/19



Drill/Tap, Drill/Mill Series
12,000/15,000-rpm, Inline-Drive Spindle
30/40 Taper – 15 hp
Standard: None
Optional: DT/DM Series




Values shown are 200% spindle load

1/2/19



Drill/Tap, Drill/Mill Series
12,000/15,000-rpm, Inline-Drive Spindle
30/40 Taper – 11.2 kW
Standard: None
Optional: DT/DM Series




Values shown are 200% spindle load

1/2/19



Drill/Tap Series
20,000-rpm, Inline-Drive Spindle
30 Taper – 15 hp
Standard: None
Optional: DT Series




Values shown are 200% spindle load

1/2/19



Drill/Tap Series
20,000-rpm, Inline-Drive Spindle
30 Taper – 11.2 kW
Standard: None
Optional: DT Series



Values shown are 200% spindle load

1/2/19