



2X  $\phi .50in^{+.001}_{-.000}$  [12.7mm<sup>+0.025</sup><sub>0.000</sub>]  $\nabla .30in$  [7.6mm]  
Dowel Pin Holes

.629in [16.0mm] Locating Key






4X  $\phi .42in$  [10.7mm]  $\nabla .86in$  [21.9mm]  
1/2-13 UNC  $\nabla .63in$  [16.0mm]  
Threaded Holes



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

\*Due to continual product improvements, machine dimensions are subject to change without notice.



**DETAIL A**  
**SCALE 1 : 1.5**

\*Due to continual product improvements, machine dimensions are subject to change without notice.