





**Mini Mill, Mini Mill-EDU**  
8000-rpm, Belt-Drive Spindle  
40 Taper – 10 hp  
Standard: MM  
Optional: MM-EDU



Values shown are 200% spindle load




**Mini Mill, Mini Mill-EDU**  
8000-rpm, Belt-Drive Spindle  
40 Taper – 7.5 kW  
Standard: MM  
Optional: MM-EDU



Values shown are 200% spindle load




**Mini Mill**  
10,000-rpm, Belt-Drive Spindle  
40 Taper – 10 hp  
Standard: none  
Optional: MM





**Mini Mill**  
10,000-rpm, Belt-Drive Spindle  
40 Taper – 7.5 kW  
Standard: none  
Optional: MM



Values shown are 200% spindle load