



2X $\varnothing .50in^{+.00}_{-.00}$ [12.7mm^{+0.0}_{0.0}] $\nabla .50in$ [12.7mm]
Dowel Pin Holes

12X $\varnothing .53in$ [13.5mm] THRU ALL
 $\varnothing .81in$ [20.6mm] $\nabla .52in$ [13.2mm]
 $\varnothing 16.40in$ [416.6mm] Bolt Hole Circle



2X $\varnothing .42in$ [10.7mm] $\nabla 1.06in$ [26.9mm]
1/2-13 UNC $\nabla .67in$ [17.1mm]




.53in [13.5mm] Tie-Down Slots

4X $\varnothing .53in$ [13.5mm] $\nabla 1.25in$ [31.8mm]
5/8-11 UNC $\nabla 1.00in$ [25.4mm]
Tapped Holes



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)

*Due to continual product improvements, machine dimensions are subject to change without notice.

Ø 31.50in
[800.1mm]
Platter Diameter



R7.00in^{+0.005}_{-.000}
[177.8mm^{+0.127}_{0.000}]



DETAIL A
SCALE 1 : 4