



Top View
Platter Rotated 90° to Base



14.30in
[363.1mm]


Top View



44.60in
[1132.8mm]


Ø 10.50in
[266.7mm]
B-Axis Part Swing

Front View
Platter Rotated 90° to Base



9.50in
[241.3mm]
A-Axis Centerline


Front View



9.37in
[238.1mm]
B-Axis Platter Height


13.38in
[339.9mm]

Eye Bolt Distance



29.5 in
[749.3 mm]

Bottom View






23.36in
[593.3mm]
Tie-Down Slots

32.80in
[833.1mm]
Tie-Down Slots

.53in
[13.5mm]

All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)

*Due to continual product improvements, machine dimensions are subject to change without notice.



DETAIL A
SCALE 2 : 3

*Due to continual product improvements, machine dimensions are subject to change without notice.