




ST Series
2400-rpm, Gearbox Drive
A2-8 – 40 hp
Standard: ST-40, ST-40L
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
2400-rpm, Gearbox Drive
A2-8 – 40 hp
Standard: ST-40, ST-40L
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
2400-rpm, Extra-Performance Spindle, Gearbox Drive
A2-8 – 55 hp
Standard: None
Optional: ST-40, ST-40L




Values shown are 200% spindle load

1/29/2016



ST Series
2400-rpm, Extra-Performance Spindle, Gearbox Drive
A2-8 – 41 kW
Standard: None
Optional: ST-40, ST-40L



Values shown are 200% spindle load

1/29/2016