




ST Series
4000-rpm, Belt-Drive Spindle
A2-6 – 20 hp
Standard: ST-15, ST-15Y, ST-20, ST-20Y
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
4000-rpm, Belt-Drive Spindle
A2-6 – 14.9 kW
Standard: ST-15, ST-15Y, ST-20, ST-20Y
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
5000-rpm, Belt-Drive Spindle
A2-6 – 30 hp
Standard: None
Optional: ST-20, ST-20Y




Values shown are 200% spindle load

1/29/2016



ST Series
5000-rpm, Belt-Drive Spindle
A2-6 – 22.4 kW
Standard: None
Optional: ST-20, ST-20Y



Values shown are 200% spindle load

1/29/2016