








Operating Dimensions**As Shipped**

All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)

*Due to continual product improvements, machine dimensions are subject to change without notice.

Air & Power

All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)

Anchor Hole Detail


Ø 5/8in [15.9mm]

▽ 2.0in [50mm]-


2.5in [66mm]

Anchor Pattern


Machine must be placed on a single, continuous concrete slab
Slab must extend 12" [305mm] beyond anchor holes in all directions



*Due to continual product improvements, machine dimensions are subject to change without notice.


Height Breakdown

All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)



Width Breakdown




All dimensions based on stackup of sheetmetal, subject to variation of 1/2" (13 mm)


*Due to continual product improvements, machine dimensions are subject to change without notice.

Table

(7x) Phantom holes are not available to use for part fixturing

T-Slot DetailTool Changer

X&Y-Axis ClearanceZ Axis Clearance at B0Table Rotation

Clearance at B90Work Envelope