




ST Series
1200-rpm, Gearbox Drive
A2-15 – 55 hp
Standard: ST-50
Optional: None




Values shown are 200% spindle load

1/29/2016



ST Series
1200-rpm, Gearbox Drive
A2-15 – 41 kW
Standard: ST-50
Optional: None



Values shown are 200% spindle load

1/29/2016