



**SMALLER FOOTPRINT + MORE TRAVEL  
THAN A VF-2? NO PROBLEM.**

# DT-3 & DM-3

HIGH-SPEED, LEAN-STYLE MACHINING CENTERS

*Built on proven Haas designs and technology, the Drill/Tap/Mill Series provides the perfect combination of speed and power to reduce cycle time and maximize shop floor space.*



Scan here or contact your  
local HFO for more details.



**STARTING AT:**

**\$71,995**



Specifications subject to change without notice. Not responsible for typographical errors. Machines shown with optional equipment. Actual product appearance may differ. Pricing subject to change without notice.

SMALL, FAST  
& POWERFUL

Drill/Tap/Mill Series machines are high-speed, lean-style machining centers with compact footprints that make very efficient use of valuable shop floor space.

PRODUCT HIGHLIGHTS

- High-performance option
- Inline direct-drive
- High accel/decel rates
- 5000-rpm rigid tapping
- 100% faster speeds and feeds
- Ultimate performance for 3D profiling

30 TAPER

DT-3



\$71,995

30 Taper / 3 Axis

Standard: 10,000 rpm  
Optional: 12k/15k/20k rpm

Side-Mount Tool Changer,  
20+1 Tool Capacity

TRAVELS

X Axis 36 in (914 mm)  
Y Axis 16 in (406 mm)  
Z Axis 15.5 in (394 mm)

SPINDLE

Max Rating 15 hp (11.2 kW)  
Max Speed 10,000 rpm  
Drive System Inline Direct-Drive  
Taper BT30

TABLE

Length 38 in (965 mm)  
Width 15 in (381 mm)  
T-Slot Width 0.626 in to 0.630 in (15.90-16.00 mm)  
T-Slot Center Distance 4.92 in (125 mm)  
Number of Std T-Slots 3  
Max Weight on Table 250 lb (113.4 kg)

40 TAPER

DM-3



\$81,995

40 Taper / 3 Axis

Standard: 10,000 rpm  
Optional: 12k/15k rpm


Side-Mount Tool Changer,  
18+1 Tool Capacity

X Axis 36 in (914 mm)  
Y Axis 16 in (406 mm)  
Z Axis 15.5 in (394 mm)


Max Rating 15 hp (11.2 kW)  
Max Speed 10,000 rpm  
Drive System Inline Direct Drive  
Taper CT/BT40

Length 38 in (965 mm)  
Width 15 in (381 mm)  
T-Slot Width 0.626 in to 0.630 in (15.90-16.00 mm)  
T-Slot Center Distance 4.92 in (125 mm)  
Number of Std T-Slots 3  
Max Weight on Table 250 lb (113.4 kg)

THE MOST X-TRAVEL YOU CAN GET,  
IN A FOOTPRINT THIS SMALL.



When every square foot counts, and every chip matters, you can't beat the optimized setup of the DT-3 or DM-3. Pound for pound, they're your best option when you want maximum cutting length in a compact CNC.



AUTOMATION READY

Take your Drill Tap/Mill productivity to the next level by adding one of our fully integrated automation systems – like the Haas HC10 Cobot. These systems operate seamlessly from the Haas control for reliable, unattended operation.





# 300,000 CONTROLS CAN'T BE WRONG.



Scan this QR Code to discover why the Haas Control is the most user-friendly CNC control in the industry.

Designed and built in-house, the Haas control is optimized specifically for Haas machine tools. It is fast, smart, and powerful, with a simple user interface and consistent, intuitive navigation that make it easy to learn and use. With more than 300,000 Haas controls in use worldwide, it clearly is an industry standard.

## Features include:

- Touchscreen Interface
- Dedicated Keypad
- One-Button Features
- Multi-Function Jog Handle
- Color LCD Screen
- Ethernet Interface
- USB Port
- M130 Media Player
- Advanced Tool Management
- 1 GB Program Memory
- Power-Failure Detection
- HaasConnect Mobile Monitoring
- WiFi Connectivity
- Safe Run
- Surge Protection
- HaasDrop Wireless File Transfer

## DON'T FORGET THE TOOLING!

We have thousands of high-quality tooling products at unbeatable low prices . . . and we're adding more every day at [www.HaasTooling.com](http://www.HaasTooling.com)



### DT-3 FOCUS

#### 30-TAPER Tooling +Workholding Kits

20-Piece, BT30 Toolholder Kit, TSC  
Part #: 08-1961



Mill Workholding Kit, 100mm (4") Manual Vise, BT30  
Part #: 08-1962



### DM-3 FOCUS

#### 40-TAPER Tooling +Workholding Kits

20-Piece, CT40 Toolholder Kit, TSC  
Part #: 08-0004A



Mill Workholding Kit, 4" Manual Vise, CT40  
Part #: 08-1993A



**Haas**  
**F1 Team**  
OFFICIAL MACHINE TOOL

Haas Automation, Inc. USA  
2800 Sturgis Rd., Oxnard, CA, USA  
[www.HaasCNC.com](http://www.HaasCNC.com) | [www.HaasTooling.com](http://www.HaasTooling.com)

Haas Automation Europe  
Mercuriusstraat 28, B-1930 Zaventem Belgium  
[www.HaasCNC.com](http://www.HaasCNC.com)