





## Leveling Pad




## Shipping Dimensions




\*All Height Dimensions Based on Suggested Leg Height

**Anchor Pattern**

## Height Breakdown



## Width Breakdown





Maintain 3 feet [915mm] clearance to the nearest obstruction around all sides of machine perimeter for maintenance access

## MAX TRAVELS


X	40.000in [1016.00mm]
Y	35.000in [889.00mm]
Z	40.000in [1016.00mm]
B	360 °

## X&amp;Y Axis Clearance




## SAE/ Inch Pallet

24 x  $\varnothing$  0.53in [13.5mm]  $\nabla$  1.75in [44.5mm]  
5/8-11 UNC  $\nabla$  1.25in [31.8mm]



## ISO/Metric Pallet

24 x  $\varnothing$  0.55in [14.0mm]  $\nabla$  1.75in [44.5mm]  
M16x2.0 - 6H  $\nabla$  1.25in [31.8mm]



Both Pallets Identical Besides Hole Dimensions

Slot Detail

Max Part Load:  
2000lb  
907.0kg

