




DIGITAL READOUT IS STANDARD  
NOT SHOWN BELOW  
ADDS 9in [228mm] HEIGHT HERE

FRONT VIEW




TOP VIEW





NO AIR REQUIRED


RIGHT SIDE VIEW




ANCHORING NOT REQUIRED


FRONT VIEW

DIGITAL READOUT IS STANDARD  
NOT SHOWN BELOW  
ADDS 9in [228mm] HEIGHT HERE



TOP VIEW






CARRIAGE, CROSS SLIDE AND  
TAILSTOCK AWAY FROM THE CHUCK


QUILL DIAMETER 2.05in [52mm]  
QUILL TRAVEL 5in [127mm]

TAILSTOCK TAPER  
MT4




CARRIAGE, CROSS SLIDE AND  
TAILSTOCK NEAR THE CHUCK


OVER BED




OVER CROSS SLIDE




MAXIMUM SWING WITH GAP CASTING REMOVED



SIDE VIEW




FRONT VIEW




CHUCK BORE MAY VARY PER BRAND

TOP VIEW




FRONT VIEW



4-STATION MANUAL TOOL POST FOR 20mm (0.787in) TOOLS

20mm [0.787]  
SQUARE SHANK  
TOOLS REQUIRED

FOLLOW REST MAXIMUM CAPACITY



STEADY REST MAXIMUM CAPACITY

