






ZERO POINT PLATTER

STANDARD HOLE PLATTER




A5 PLATTER


T-SLOT PLATTER





BOTTOM HOLE DIMENSIONS




- 8X Ø .27in[6.8mm] THRU ALL
- Ø 0.41in[10.3mm] ∇ .26in[6.5mm]
- 8X Ø .16in[4.0mm] ∇ .49in[12.4mm]
- 10-32UNF-2B ∇ .38in[9.7mm]





NOTE: BHC AND SPINDLE NOSE DIMENSIONS ARE PER AMERICAN STANDARD BULLETIN ASA B5.9-1960





***NOTE:** MAXIMUM HOLE DRILL DEPTH IN PLATTER IS 1.1" USING DRILL TIP AS REFERENCE.
DO NOT DRILL THRU PLATTER.