



DIGITAL READOUT IS STANDARD  
NOT SHOWN BELOW  
ADDS 9in [228mm] HEIGHT HERE


FRONT VIEW



TOP VIEW




REAR VIEW



NO AIR REQUIRED


RIGHT SIDE VIEW

ANCHORING  
NOT REQUIRED





DIGITAL READOUT IS STANDARD  
NOT SHOWN BELOW  
ADDS 9in [228mm] HEIGHT HERE

FRONT VIEW



TOP VIEW






CARRIAGE, CROSS SLIDE AND  
TAILSTOCK AWAY FROM THE CHUCK


TAILSTOCK TAPER  
MT4

QUILL DIAMETER 2.32in [59mm]  
QUILL TRAVEL 5in [127mm]




CARRIAGE, CROSS SLIDE AND  
TAILSTOCK NEAR THE CHUCK


OVER BED




OVER CROSS SLIDE




MAXIMUM SWING WITH GAP CASTING REMOVED



SIDE VIEW




FRONT VIEW




CHUCK BORE MAY VARY PER BRAND


TOP VIEW




FRONT VIEW




4-STATION MANUAL TOOL POST FOR 20mm (0.787in) TOOLS




FOLLOW MAXIMUM  
 $\varnothing$  3.4in [  $\varnothing$  86.4mm]



FOLLOW MINIMUM  
 $\varnothing$  0.6in [  $\varnothing$  15.2mm]



STEADY MAXIMUM  
 $\varnothing$  8.27in [  $\varnothing$  210mm]



STEADY MINIMUM  
 $\varnothing$  1.5in [  $\varnothing$  38mm]