





FRONT VIEW




TOP VIEW






REAR VIEW



NO AIR REQUIRED


RIGHT SIDE VIEW

ANCHORING
NOT REQUIRED







FRONT VIEW



TOP VIEW






CARRIAGE, CROSS SLIDE AND
TAILSTOCK AWAY FROM THE CHUCK

TAILSTOCK TAPER
MT4


QUILL DIAMETER 2.32in [59mm]
QUILL TRAVEL 5in [127mm]




CARRIAGE, CROSS SLIDE AND
TAILSTOCK NEAR THE CHUCK





OVER BED



OVER CROSS SLIDE




MAXIMUM SWING WITH GAP CASTING REMOVED







SIDE VIEW




FRONT VIEW




TOP VIEW




FRONT VIEW




4-STATION MANUAL TOOL POST FOR 25MM (1.00 in) TOOLS




FOLLOW MAXIMUM
 $\phi 3.4\text{in}$ [$\phi 86.4\text{mm}$]



FOLLOW MINIMUM
 $\phi 0.6\text{in}$ [$\phi 15.2\text{mm}$]



STEADY MAXIMUM
 $\phi 8.27\text{in}$ [210mm]



STEADY MINIMUM
 $\phi 1.5\text{in}$ [38mm]