




DC-Series Drill Centers
Inline-Drive Spindles
30 Taper – 15 hp
Standard: 10,000-rpm
Optional: 15,000-rpm, 20,000-rpm





DC-Series Drill Centers
Inline-Drive Spindles
30 Taper – 11.2 kW
Standard: 10,000-rpm
Optional: 15,000-rpm, 20,000-rpm

