





**DC-Series Drill Centers**  
Inline-Drive Spindles  
30 Taper – 15 hp  
Standard: 10,000-rpm  
Optional: 15,000-rpm, 20,000-rpm



Values shown are 200% spindle load



**DC-Series Drill Centers**  
Inline-Drive Spindles  
30 Taper – 11.2 kW  
Standard: 10,000-rpm  
Optional: 15,000-rpm, 20,000-rpm



Values shown are 200% spindle load