





Mini Mill-EDU
6000-rpm, Belt-Drive Spindle
40 Taper – 10 hp
Standard: MM-EDU
Optional: None






Mini Mill-EDU
6000-rpm, Belt-Drive Spindle
40 Taper – 7.5 kW
Standard: MM-EDU
Optional: None



Values shown are 200% spindle load




Mini Mill, Mini Mill-EDU
8000-rpm, Belt-Drive Spindle
40 Taper – 10 hp
Standard: MM
Optional: MM-EDU



Values shown are 200% spindle load



Mini Mill, Mini Mill-EDU
8000-rpm, Belt-Drive Spindle
40 Taper – 7.5 kW
Standard: MM
Optional: MM-EDU



Values shown are 200% spindle load