






## INSTALLED DIMENSIONS




## SHIPPING DIMENSIONS




All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

## OPERATIONAL HEIGHT



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

## OPERATIONAL WIDTH AND DEPTH



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

## FRONT LOADING AUTO-DOOR





TABLE HEIGHT IS  
33.6in (853mm)

All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)


## SIDE LOADING AUTO-WINDOW

HEIGHTS MAY VARY  
BASED ON  
INSTALLATION HEIGHT



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

## AIR &amp; POWER



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

## Anchor Hole Detail:


Ø 0.625in [16mm]

▽ 2.0in to 2.25in

▽ 51mm to 57mm


## ANCHORING PATTERN

Anchoring kit available  
includes floor template  
& hardware needed




Note: Machine must be placed on one continuous concrete slab. Slab should extend 12in [305mm] beyond anchor holes in all directions


## X &amp; Y AXIS TRAVELS



## Z-AXIS TRAVEL



TABLE



All dimensions based on stackup of sheetmetal, subject to variation of 1/2" ( 13 mm)

TOOL CHANGER

