



Top View
Platter Rotated 90° to Base




Front View
Platter Rotated 90° to Base




33.25in
[844.6mm]
Eye Bolt Center Distance

Ø 19.19in
[487.4mm]
A-Axis Clearance at 90°




.53in
[13.5mm]
Tie-Down Slots

Top View



Ø 23.50in
[596.9mm]
B-Axis Part Swing
Max part swing reduced
at tilt angles greater than ±75°


Front View



11.87in
[301.6mm]
B-Axis Platter Height



16.88in
[428.8mm]

Bottom View





26.21in
[665.7mm]
Tie-Down Slots

37.14in
[943.4mm]
Tie-Down Slots



DETAIL A
SCALE 1 : 2

Optional 350MM Platter



DETAIL B
SCALE 2 : 5

