










\* Add 8in for Extended Z-Clearance Option



Shipping Dimensions



Air & Power




Maintain 3 feet [915mm] clearance to the nearest obstruction around all sides of machine perimeter for maintenance access

Anchor Pattern

For machines built before Sept. 2023.

**NOTE: For machines built after Sept. 2023, see separate Anchoring Template.**




For precise locations and specifications please use template included in the Anchoring Kit and instructions found on Haascnc.com




Height Breakdown

\* Add 8in for Extended Z-Clearance Option




Width Breakdown






X&Y-Axis Travel and Clearance




Z-AXIS TRAVEL & CLEARANCE

\* Add 8in for Extended Z-Clearance Option






Table



16mm T-SLOTS



T-Slot Dimensions in inches

Slot Size	A	B	C	D	E	F
12mm	$0.438 \begin{smallmatrix} +.002 \\ -.000 \end{smallmatrix}$	$0.76 \pm 0.02$	$0.310 \pm 0.010$	$0.318 \pm 0.010$	$0.03 \times 45^\circ$	$0.020 \times 45^\circ$
16mm	$0.628 \pm 0.002$	$1.06 \pm 0.02$	$0.640 \pm 0.010$	$0.420 \pm 0.010$	$0.06 \times 45^\circ$	$0.020 \times 45^\circ$

\* Add 8in for Extended Z-Clearance Option

Tool Changer

